

Product data sheet

Specifications



Emergency exit sign, Exiway Smartexit, Activa, maintained and non maintained, 32m, 3h, white

OVA48407

Main

Range	Exiway
Product Name	Exiway Smartexit Activa
Product Or Component Type	Emergency exit sign
Device Application	EMERGENCY Lighting
Function	Self-test
Colour	White
Supply	Maintained Non-maintained
Provided Equipment	With 4 standard stickers (left/right/down/down)
Main Colour Tint	White
Colour Tint	White

Complementary

[Us] Rated Supply Voltage	230 V
Light Source	LED
Light Source Colour	White
Power Consumption In Va	5.61 VA
Power Consumption In W	2.77 W
Battery Capacity	1.5 Ah at 3.2 V, LiFePO4
Device Mounting	Surface direct fixing Ceiling direct fixing Flag direct fixing Hanging wall Hanging ceiling
Visibility Distance	32 m
Charging Time	12 h
Autonomy	3 h
Bulb Type	LED 100000 h
Material	Polycarbonate self-extinguishing PMMA (polymethyl methacrylate)
Height	260 mm
Width	190 mm
Depth	45 mm
Net Weight	0.7 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ip Degree Of Protection	IP40
Ambient Air Temperature For Operation	0...40 °C
Fire Resistance	850 °C
Standards	EN/IEC 60598-2-22 EN/IEC 62471 EN 62034

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	22.0 cm
Package 1 Length	33.0 cm
Package 1 Weight	900.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information