

# Product data sheet

Specifications



## Pragma surface interface - IP30 - 2 x 18 modules - without door

PRA08218

⚠ Discontinued on: Jul 17, 2020

⚠ End-of-service on: Sep 22, 2020

⚠ Discontinued

### Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Interface
Width	200 mm outside:
Height	450 mm
Depth	115 mm
Nb Of 18 Mm Modules Per Row	18
Nb Of Horizontal Rows	2
Electrical Insulation Class	Double insulation Class II
Provided Equipment	1 x identification label 1 x plain plate per row 1 x front face and back connection
Type Of Door	Without

### Complementary

Enclosure Mounting	Surface
9 Mm Pitches	36
Total Number Of 18 Mm Modules	14
Number Of Plates	2 for plain plate
[In] Rated Current	125 A
[Ui] Rated Insulation Voltage	400 V
Type Of Rail	Without
Mounting Plate Description	Without mounting plate
Cable Entry	Removable plates Cable or tube Trunking Cut-out plates
Enclosure Material	Back part: technoplastic Front face: technoplastic
Colour	Enclosure: white (RAL 9016) Front face: white (RAL 9016)
Embedding Depth	0 mm
Internal Depth	95 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Fire Resistance	Back part: 750 °C Front face: 750 °C
Ip Degree Of Protection	IP30 without door IP40 with door
Ik Degree Of Protection	IK08 without door IK09 with door
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 60670-1 IEC 60670-24 IEC 61439-1 IEC 61439-3

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.5 cm
Package 1 Width	22 cm
Package 1 Length	46 cm
Package 1 Weight	1.7 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>