

# Product data sheet

Specifications



## Pragma - single or three phase control block - flush - 18 modules - without door

PRA51818

 **Discontinued on:** Oct 31, 2023

 **Discontinued**

### Main

Range Of Product	Pragma
Product Or Component Type	Control block
Accessory / Separate Part Category	Installation accessory
Network Connection	Three phase Single phase
Installed Device	DB 90

### Complementary

Range Compatibility	Pragma
Enclosure Mounting	Flush
Number Of Horizontal Rows	2
9 Mm Pitches	36
Number Of 18 Mm Modules Per Row	18
Total Number Of 18 Mm Modules	18
Provided Equipment	DIN rail 2 36
Enclosure Material	Technoplastic
Width	426 mm
Height	450 mm
Depth	123 mm
Colour	Titanium white

### Environment

Product Certifications	EDF
Electrical Insulation Class	Class II
Fire Resistance	Front face: 750 °C
Ip Degree Of Protection	IP30
Ik Degree Of Protection	IK08
Ambient Air Temperature For Operation	-25...60 °C

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	13.500 cm
Package 1 Width	51.000 cm
Package 1 Length	53.000 cm
Package 1 Weight	5.500 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	24
Package 2 Height	120.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	144.000 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">Circularity Profile</a>