

# Product data sheet

Specifications

## Resi9 Trunking end 18 Modules

R9H18539



### Main

Range	Resi9
Product Or Component Type	End cover
Accessory / Separate Part Category	Trunking accessory
Range Compatibility	Opale Resi9
Number Of 18 Mm Modules Per Row	18
Standards	NFC 15-100 NF EN 50085-2-1

### Complementary

Material	Plastic
Fire Resistance	750 °C conforming to EN/IEC 60695-2-11
Ip Degree Of Protection	IP40 conforming to EN/IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262 IK08 conforming to EN 50102
Quantity Per Set	Set of 1
Height	35 mm
Width	364 mm
Depth	66 mm
Colour	White (RAL 9003)

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	6.600 cm
Package 1 Length	36.300 cm
Package 1 Weight	133.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	42
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	6.188 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	84
Package 3 Height	45.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	50.000 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations