

# Product data sheet

Specifications



## Resi9 Insulating plate PLUS 1x13 Modules

R9H13991

### Main

|                                    |                                    |
|------------------------------------|------------------------------------|
| Range                              | Resi9                              |
| Product Or Component Type          | Insulating plate                   |
| Accessory / Separate Part Category | Insulation accessory               |
| Range Compatibility                | Opale enclosure<br>Resi9 enclosure |

### Complementary

|                                 |                            |
|---------------------------------|----------------------------|
| Number Of Horizontal Rows       | 1                          |
| Number Of 18 Mm Modules Per Row | 13                         |
| Total Number Of 18 Mm Modules   | 13                         |
| Provided Equipment              | 2 plug<br>1 plastic bottom |
| Net Weight                      | 220 g                      |
| Width                           | 252 mm                     |
| Height                          | 250 mm                     |
| Depth                           | 12 mm                      |

### Environment

|                         |   |
|-------------------------|---|
| Fire Resistance         | 750 °C conforming to EN/IEC 60695-2-11                      |
| Ip Degree Of Protection | IP30 conforming to EN/IEC 60529                             |
| Ik Degree Of Protection | IK08 conforming to IEC 62262<br>IK08 conforming to EN 50102 |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 2.0 cm  |
| Package 1 Width              | 25.2 cm |
| Package 1 Length             | 25.2 cm |
| Package 1 Weight             | 243.0 g |
| Unit Type Of Package 2       | S03     |
| Number Of Units In Package 2 | 15      |
| Package 2 Height             | 30.0 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                  |         |
|------------------|---------|
| Package 2 Width  | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 4.15 kg |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)