

Product data sheet

Specifications

Cover frame, Odace Styl, 4 gangs, grey



S520708A1

Main

Range Of Product	Odace
Aesthetic Name	Styl
Product Or Component Type	Cover frame
Number Of Gangs	4 gangs
Installation Direction	Horizontal/vertical
Distance Between Centers	71 mm
Type Of Frame	Quadruple
Type Of Packing	Flow-pack

Complementary

Device Mounting	Flush
Fixing Mode	Clip-in
Colour Tint	Grey (Pantone 3C)
Surface Finish	Matt
Surface Treatment	Painted
Material	Thermoplastic ABS-UV stabilised: decorative frame
Height	85 mm
Width	298 mm
Depth	10 mm
Net Weight	0.03875 kg
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	5...45 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	NF C 61-314 EN 60669-1 UNE 20315-1-1 2006/95/EEC
Product Certifications	AENOR: 030/2205 LCIE: NF 603415A N NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	8.6 cm
Package 1 Length	32.8 cm
Package 1 Weight	40 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	5.5 cm
Package 2 Width	8.8 cm
Package 2 Length	37 cm
Package 2 Weight	258 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	10
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	723 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

✓ Sustainable Packaging

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations