

Product data sheet

Specifications



Cover frame, Odace Styl, 1 gang, white

S520712

Main

Range Of Product	Odace
Aesthetic Name	Odace Styl Pratic
Product Or Component Type	Cover frame
Number Of Gangs	1 gang
Cover Type	Mobile support
Type Of Frame	Single
Type Of Packing	Flow-pack

Complementary

Device Mounting	Flush
Fixing Mode	Clip-in
Colour Tint	White (RAL 9003)
Surface Finish	Glossy
Material	Thermoplastic ABS-UV stabilised: decorative frame
Height	102 mm
Width	85 mm
Depth	28 mm
Net Weight	0.01893 kg
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	5...45 °C
Standards	NF C 61-314 2006/95/EEC EN 60669-1 UNE 20315-1-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	AENOR: 030/2205 LCIE: NF 603415A N NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	9.0 cm
Package 1 Length	11.0 cm
Package 1 Weight	21.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	2
Package 2 Height	10.7 cm
Package 2 Width	16.6 cm
Package 2 Length	4.8 cm
Package 2 Weight	82.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	56
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	2.754 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

✓ Sustainable Packaging

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations