

Product data sheet

Specifications



Cover frame, Odace Touch, 1 gang, anthracite

S54C802P4

Main

Range Of Product	Odace
Aesthetic Name	Touch
Product Or Component Type	Cover frame
Type Of Frame	Single
Quantity Per Set	Set of 1
Condition Of Use	Indoor

Complementary

Device Mounting	Flush
Fixing Mode	Clip-in
Colour Tint	Wood zebrano
Side Color	Anthracite (RAL 7021)
Surface Finish	Matt
Material	PC (polycarbonate): decorative frame Aluminium
Height	85 mm
Width	85 mm
Depth	10 mm
Net Weight	0.01298 kg
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	5...45 °C
Standards	NF C 61-314 UNE 20315-1-1 EN 60669-1 2006/95/EEC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	AENOR: 030/2205 LCIE: CCA-FR_598285B LCIE: NF 603415A N NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.4 cm
Package 1 Width	9.8 cm
Package 1 Length	13 cm
Package 1 Weight	26 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	5
Package 2 Height	13.7 cm
Package 2 Width	10.3 cm
Package 2 Length	19.3 cm
Package 2 Weight	186 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations