

# Product data sheet

Specifications



## Orion - blind cover 4X2 - beige

S730100064

### Main

|                           |               |
|---------------------------|---------------|
| Range                     | Orion         |
| Aesthetic Name            | Orion Essence |
| Product Or Component Type | Blind cover   |

### Complementary

|                                       |   |
|---------------------------------------|---|
| Device Mounting                       | Flush   |
| Fixing Mode                           | Clip-in   |
| Colour Tint                           | Beige (Pantone 7530C)                             |
| Surface Finish                        | Glossy  |
| Surface Treatment                     | Untreated   |
| Type Of Packing                       | Flow-pack   |
| Quantity Per Set                      | Set of 20   |
| Ambient Air Temperature For Storage   | -5...50 °C  |
| Ambient Air Temperature For Operation | -5...35 °C  |
| Material                              | Thermoplastic ABS-UV stabilised: decorative frame |
| Height                                | 120 mm  |
| Width                                 | 82.5 mm   |
| Depth                                 | 7.9 mm  |
| Net Weight                            | 0.0213 kg   |

### Environment

|                              |   |
|------------------------------|---|
| Ik Degree Of Protection      | IK07  |
| Ip Degree Of Protection      | IP21D   |
| Environmental Characteristic | Alcohol<br>Bleach<br>Liquid soap<br>Window-cleaning fluid<br>Hydrogen peroxide (H2O2)<br>Petrol<br>Acetone<br>Oil<br>UV resistant |

### Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type Of Package 1       | PCE |
| Number Of Units In Package 1 | 1   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                  |         |
|------------------|---------|
| Package 1 Height | 0.8 cm  |
| Package 1 Width  | 9.3 cm  |
| Package 1 Length | 20.0 cm |
| Package 1 Weight | 23.0 g  |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

## Certifications & Standards

|                       |   |
|-----------------------|---|
| Reach Regulation      | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive     | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Circularity Profile   | <a href="#">End of Life Information</a>   |