

# Product data sheet

Specifications



## Cover frame, Odace Touch, 3 gangs, aluminium

S530816J1

### Main

Range Of Product	Odace
Aesthetic Name	Touch
Product Or Component Type	Cover frame
Number Of Gangs	3 gangs
Installation Direction	Vertical
Distance Between Centers	57 mm
Type Of Frame	Triple
Type Of Packing	Flow-pack

### Complementary

Device Mounting	Flush
Fixing Mode	Clip-in
Colour Tint	Aluminium croco
Surface Finish	Brushed
Material	Aluminium PC (polycarbonate)
Height	199 mm
Width	85 mm
Depth	10 mm
Net Weight	0.02558 kg
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

### Environment

Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	5...45 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	NF C 61-314 EN 60669-1 2006/95/EEC UNE 20315-1-1 NBN C 61-112-1
Product Certifications	N NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	8.5 cm
Package 1 Length	19.8 cm
Package 1 Weight	41 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	5.8 cm
Package 2 Width	9 cm
Package 2 Length	37 cm
Package 2 Weight	263 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	30
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	1.884 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging   Transparency   RoHS/REACH

## Resource performance

✓ Sustainable Packaging

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations