


# Product data sheet

Specifications

## Cover frame, Odace Touch, 4 gangs, anthracite



S540808K1

 **Discontinued on:** Dec 17, 2020

 **Discontinued**

### Main

Range Of Product	Odace
Aesthetic Name	Touch
Product Or Component Type	Cover frame
Number Of Gangs	4 gangs
Installation Direction	Horizontal/vertical
Distance Between Centers	71 mm
Type Of Frame	Quadruple
Type Of Packing	Flow-pack

### Complementary

Device Mounting	Flush
Fixing Mode	Clip-in
Colour Tint	Smoked
Side Color	Anthracite
Surface Finish	Glossy
Material	Aluminium: decorative frame PC (polycarbonate)
Height	85 mm
Width	298 mm
Depth	10 mm
Net Weight	0.0395 kg
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

### Environment

Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	5...45 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60669-1 NBN C 61-112-1 2006/95/EEC NF C 61-314 UNE 20315-1-1
Product Certifications	N NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	8.5 cm
Package 1 Length	29.8 cm
Package 1 Weight	69 g

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information