

Product data sheet

Specifications

Cover frame, Odace Touch, 4 gangs, anthracite



S540808P3

⚠ Discontinued on: Dec 17, 2020

⚠ Discontinued

Main

Range Of Product	Odace
Aesthetic Name	Touch
Product Or Component Type	Cover frame
Number Of Gangs	4 gangs
Installation Direction	Horizontal/vertical
Distance Between Centers	71 mm
Type Of Frame	Quadruple
Type Of Packing	Flow-pack

Complementary

Device Mounting	Flush
Fixing Mode	Clip-in
Colour Tint	Wood ash
Side Color	Anthracite
Surface Finish	Brushed
Material	PC (polycarbonate): decorative frame Aluminium
Height	85 mm
Width	298 mm
Depth	10 mm
Net Weight	0.0395 kg
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	5...45 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60669-1 NBN C 61-112-1 NF C 61-314 2006/95/EEC UNE 20315-1-1
Product Certifications	AENOR: 030/2205 LCIE: NF 603415A N NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	8.5 cm
Package 1 Length	29.8 cm
Package 1 Weight	62 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information