

Product data sheet

Specifications



Orion - duplex American socket outlet 2P+E 20A 125V hospital grade with fixing-f

S703330045

⚠ Discontinued on: Dec 15, 2021

⚠ Discontinued

Main

Range Of Product	Orion
Range	Orion
Product Or Component Type	Socket-outlet
Device Presentation	Mechanism with fixing frame
Outlet Poles Configuration	2P + E without shutter
Fixing Mode	By screws
Type Of Packing	Flow-pack
Quantity Per Set	Set of 10
Sale Per Indivisible Quantity	1
Rated Current	20 A at 125 V AC 60 Hz

Complementary

Number Of Power Socket Outlets	2
Device Mounting	Flush
Outlet Standard Description	Hospital grade
Outlet Standard	American
Ground Lug Position	Straight 0° position
Number Of Modules	3 modules 120 x 82.5 mm
Surface Finish	Glossy
Surface Treatment	Untreated
Ambient Air Temperature For Storage	-20...60 °C
Dielectric Strength	2000 V
Ambient Air Temperature For Operation	-5...35 °C
Electrical Durability	5000 cycles
Connections - Terminals	3 screw terminals
Screwdriver Shape	Phillips
Number Of Cables	2
Clamping Connection Capacity	1.5...4 mm ² for rigid cable(s) 1.5...4 mm ² for stranded cable(s) 1.5...4 mm ² for flexible cable(s)
Wire Stripping Length	18 mm

Material	PC (polycarbonate) GF10 FR: casing PA (polyamide): centre plate ABS (acrylonitrile butadiene-styrene): adaptor frame
Height	113 mm
Width	71 mm
Depth	40.4 mm
Embedding Depth	31.5 mm
Net Weight	0.134 kg
Standards	UL 498 UL 943 UL 94

Environment

Product Certifications	NOM
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20
Environmental Characteristic	Alcohol Window-cleaning fluid Oil Bleach Hydrogen peroxide (H2O2) Petrol Liquid soap UV resistant Acetone

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
