

Product data sheet

Specifications



Séquence5 - cable outlet - 16 A - 6...12 mm - Nickel

S800662NB

⚠ Discontinued on: Jul 26, 2021

⚠ End-of-service on: Aug 19, 2021

⚠ Discontinued

Main

Range	Sequence5
Product Or Component Type	Cable outlet
Device Presentation	Complete product
Product Specific Application	Exit wire for electrical heating
Type Of Packing	Box
Quantity Per Set	Set of 1
Sale Per Indivisible Quantity	1

Complementary

Device Mounting	Flush
Rated Current	16 A
Fixing Mode	By screws
Colour Tint	Nickel
Surface Finish	Glossy
Connections - Terminals	Screw
Number Of Loop Terminals	2
Shape Of Screw Head	Pozidriv No 1
Clamping Connection Capacity	1 x 1.5...1 x 2.5 mm ² for rigid cable(s) 1 x 1.5...1 x 2.5 mm ² for flexible cable(s) 1 x 1.5...1 x 2.5 mm ² for stranded cable(s)
Cable Outer Diameter	6...12 mm
Wire Stripping Length	12 mm
Material	Metal
Height	80 mm
Width	80 mm
Depth	38 mm
Embedding Depth	19 mm
Net Weight	0.183 kg

Environment

Ambient Air Temperature For Storage	-5...50 °C
-------------------------------------	------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	5...35 °C
Standards	UTE C 61-392 EN 60669-1
Product Certifications	LCIE: NF 603415A NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP2XC
Environmental Characteristic	Alcohol UV resistant Window-cleaning fluid Oil Acetone Bleach Petrol Liquid soap

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	10 cm
Package 1 Length	12.5 cm
Package 1 Weight	218 g

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	Product out of China RoHS scope. Substance declaration for your information