

Product data sheet

Specifications



Sedna - double 2way switch - 10AX white

SDN0690121

 **Discontinued on:** Dec 30, 2023

 **Discontinued**

Main

Range Name	Sedna
Product Or Component Type	Switch
Delivery Form	Complete product
Kind Of Terminals	Screwless terminals
Cover Plate Color	White
Function	Double 2-way
Rated Current	10 AX at 250 V AC

Complementary

Installation	Flush
Height	80 mm
Material Of Visible Parts	Thermoplastic ABS-UV stabilised
Power Range	2300 W
Net Weight	0.0955 kg
Depth Of Visual Part	12 mm
Wire Structure	Flexible Rigid
Depth	37 mm
Surface Finish	Glossy
Width	85 mm
Wire Stripping Length	13 mm
Fixing Mode	Screws or claws 51...70 mm
Terminal Capacity	2 cable(s) 2.5 mm²

Environment

Ip Degree Of Protection	IP20
Conformity Mark	CE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	5.000 cm
Package 1 Width	11.000 cm
Package 1 Length	15.000 cm
Package 1 Weight	90.800 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	10.000 cm
Package 2 Width	20.500 cm
Package 2 Length	31.000 cm
Package 2 Weight	853.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	40
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	4.608 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations