

Product data sheet

Specifications



Sedna - 1pole push-button - locator lamp (Bell symbol) white DIY

SDN1700221

 **Discontinued on:** Dec 30, 2023

 **Discontinued**

Main

Range Name	Sedna
Product Or Component Type	Push-button
Delivery Form	Complete product
Kind Of Terminals	Screwless terminals
Cover Plate Color	White
Function	1-pole push-button
Type Of Packing	Blister
Rated Current	10 AX at 250 V AC

Complementary

Installation	Flush
Height	80 mm
Material Of Visible Parts	Thermoplastic ABS-UV stabilised
Pilot Light	Blue locator lamp
Power Range	2300 W
Net Weight	0.06396 kg
Depth Of Visual Part	12 mm
Wire Structure	Flexible Rigid
Depth	37 mm
Surface Finish	Glossy
Width	85 mm
Wire Stripping Length	13 mm
Fixing Mode	Screws or claws 51...70 mm
Terminal Capacity	2 cable(s) 2.5 mm²

Environment

Ip Degree Of Protection	IP20
Conformity Mark	CE

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	8.100 cm
Package 1 Length	8.100 cm
Package 1 Weight	116.000 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	40
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	5.290 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	160
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	33.160 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations