


# Product data sheet

Specifications



## Dimmer, Sedna, rotary, 325VA, beige

SDN2200647

⚠ Discontinued on: Dec 30, 2023

⚠ Discontinued

### Main

Range Of Product	Sedna
Product Or Component Type	Dimmer
Device Presentation	Mechanism with fixing frame
Device Application	Light control
Colour Tint	Beige
Kind Of Terminals	Pillar terminals

### Complementary

Device Mounting	Flush
Dimmer Control	Rotary push type
Load Type	230 V AC halogen lamp: 25...325 W Low voltage halogen lamp with electronic transformer: 25...325 VA 230 V AC incandescent lamp: 25...325 W
Rated Voltage	230 V AC
Protection Type	Electronic fuse protection
Main Colour Tint	Beige
Material	Thermoplastic ABS-UV stabilised
Surface Finish	Glossy
Terminal Capacity	1 cable(s) 2.5 mm²
Wire Structure	Flexible Rigid
Wire Stripping Length	7 mm
Fixing Mode	Claws, span of claws working range: 51...80 mm Screws
Height	71 mm
Width	71 mm
Depth	47.5 mm
Depth Of Visual Part	20 mm
Net Weight	0.10555 kg
Market Segment	Residential Small commercial

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60669-2-1
Conformity Mark	CE
Product Certifications	GOST-R
Ip Degree Of Protection	IP20

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.1 cm
Package 1 Width	7.1 cm
Package 1 Length	4.75 cm
Package 1 Weight	105.55 g

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins