


Product data sheet

Specifications



Sedna - hotel card switch - 10AX without frame cream

SDN1900123

 **Discontinued on:** Dec 30, 2023

 **Discontinued**

Main

Range	Sedna
Function	Card switch
Device Application	Control
Delivery Form	Without frame

Complementary

Function	Hotel card switch
Power Range	2300 W
Rated Current	10 AX at 250 V AC
Kind Of Terminals	Screwless terminals
Terminal Capacity	2 cable(s) 2.5 mm²
Wire Structure	Rigid Flexible
Wire Stripping Length	13 mm
Material Of Visible Parts	Thermoplastic ABS-UV stabilised
Surface Finish	Glossy
Fixing Mode	Claws, span of claws working range: 51...70 mm Screws
Height	75 mm
Width	71 mm
Depth	55 mm
Depth Of Visual Part	31 mm
Net Weight	0.063563 kg

Environment

Ip Degree Of Protection	IP20
Conformity Mark	CE
Product Certifications	GOST-R

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	5.000 cm
Package 1 Width	7.000 cm
Package 1 Length	8.000 cm
Package 1 Weight	70.500 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.500 cm
Package 2 Width	18.500 cm
Package 2 Length	27.500 cm
Package 2 Weight	643.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	96
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	8.377 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations