

Product data sheet

Specifications



Presence detector, Sedna, 10A, titanium

SDN2000268

 **Discontinued on:** Dec 30, 2023

 **Discontinued**

Main

Range	Sedna
Product Or Component Type	Presence detector
Device Application	Light control
Device Presentation	Mechanism with fixing frame
Sensor Type	PIR
Colour Tint	Titanium
Product Specific Application	Staircase monitoring

Complementary

Device Mounting	Flush
Power Range	2300 W
Rated Current	10 A at 230 V AC 50 Hz
Function Available	Automatic with manual override
Light Intensity Adjustment	5...1000 lux
Time Delay	2 s...20 min
Horizontal Detection Angle	0...180 °
Connections - Terminals	Pillar terminals
Terminal Capacity	1 cable(s) 2.5 mm ²
Wire Structure	Rigid Flexible
Wire Stripping Length	8 mm
Fixing Mode	Screws
Material Of Visible Parts	Thermoplastic ABS-UV stabilised
Surface Finish	Glossy
Minimum Mounting Height	1.2 m
Height	71 mm
Width	71 mm
Depth	51.4 mm
Net Weight	0.09719 kg
Depth Of Visual Part	26.6 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Conformity Mark	CE
Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	0...35 °C
Product Certifications	GOST-R

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.1 cm
Package 1 Width	7.1 cm
Package 1 Length	5.14 cm
Package 1 Weight	97.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	96
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	11.471 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins