

Product data sheet

Specifications



Sedna - single socket outlet, pin earth - 16A IP44 shutters, lid, cream

SDN2890323

⚠ Discontinued on: Dec 30, 2023

⚠ Discontinued

Main

Range	Sedna
Product Or Component Type	Socket-outlet
Outlet Standard Description	Pin earth
Delivery Form	Complete product
Additional Features	Lid and shuttered
Rated Current	16 A at 250 V AC
Cover Plate Color	Cream
Kind Of Terminals	Lift terminals

Complementary

Installation	Flush
Power Range	3680 W
Terminal Capacity	2 cable(s) 2.5 mm²
Wire Structure	Rigid Flexible
Wire Stripping Length	13 mm
Material Of Visible Parts	ASA + PC
Surface Finish	Glossy
Fixing Mode	Screws or claws 52...69 mm
Height	85 mm
Width	85 mm
Depth	46.3 mm
Depth Of Visual Part	18 mm
Net Weight	0.095496 kg

Environment

Ip Degree Of Protection	IP44
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	6.500 cm
Package 1 Width	11.000 cm
Package 1 Length	15.000 cm
Package 1 Weight	109.200 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	10.000 cm
Package 2 Width	20.000 cm
Package 2 Length	31.000 cm
Package 2 Weight	772.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	30
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	4.259 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations