


# Product data sheet

Specifications



## Sedna - single socket outlet, pin earth - 16A IP44 shutters, lid, wo frame alum

SDN2800360

⚠ Discontinued on: Dec 30, 2023

⚠ Discontinued

### Main

Range Name	Sedna
Function	Socket-outlet
Delivery Form	Without frame
Outlet Poles Configuration	2P + E with shutters
Outlet Standard Description	Pin earth
Rated Current	16 A at 250 V AC
Market Segment	Small commercial Residential
Socket Additional Information	Lid

### Complementary

Wire Stripping Length	13 mm
Width	71 mm
Depth	46.3 mm
Net Weight	0.078782 kg
Depth Of Visual Part	18 mm
Fixing Mode	Claws, span of claws working range: 52...69 mm Screws
Height	71 mm
Surface Finish	Glossy
Material Of Visible Parts	PC
Wire Structure	Rigid Flexible
Terminal Capacity	2 cable(s) 2.5 mm²
Kind Of Terminals	Lift terminals
Power Range	3680 W

### Environment

Ip Degree Of Protection	IP44
Product Certifications	B
Standards	IEC 60884-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	7.000 cm
Package 1 Length	7.000 cm
Package 1 Weight	78.500 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.500 cm
Package 2 Width	18.500 cm
Package 2 Length	27.500 cm
Package 2 Weight	868.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	11.060 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓   Reach Free Of Svhc

✓   Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations