


# Product data sheet

Specifications



## Sedna - single socket outlet, side earth - 16A, screwless, without frame al

SDN3001860

⚠ Discontinued on: Dec 30, 2023

⚠ Discontinued

### Main

|                             |                                 |
|-----------------------------|---------------------------------|
| Range Name                  | Sedna                           |
| Function                    | Socket-outlet                   |
| Delivery Form               | Without frame                   |
| Outlet Poles Configuration  | 2P + E                          |
| Outlet Standard Description | Side earth                      |
| Outlet Standard             | Poland                          |
| Rated Current               | 16 A at 250 V AC                |
| Market Segment              | Residential<br>Small commercial |

### Complementary

|                           |   |
|---------------------------|---|
| Wire Stripping Length     | 13 mm   |
| Width                     | 71 mm   |
| Depth                     | 41.3 mm   |
| Net Weight                | 0.06214 kg  |
| Depth Of Visual Part      | 10 mm   |
| Fixing Mode               | Screws52...69 mm<br>Claws, span of claws working range: |
| Height                    | 71 mm   |
| Surface Finish            | Glossy  |
| Material Of Visible Parts | PC  |
| Wire Structure            | Flexible<br>Rigid                                       |
| Terminal Capacity         | 2 cable(s) 2.5 mm²                                      |
| Kind Of Terminals         | Screwless terminals                                     |
| Power Range               | 3680 W  |

### Environment

|                         |             |
|-------------------------|-------------|
| Ip Degree Of Protection | IP20        |
| Product Certifications  | GOST-R      |
| Standards               | IEC 60884-1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 4.000 cm  |
| Package 1 Width              | 7.000 cm  |
| Package 1 Length             | 7.000 cm  |
| Package 1 Weight             | 64.100 g  |
| Unit Type Of Package 2       | BB1       |
| Number Of Units In Package 2 | 10        |
| Package 2 Height             | 9.500 cm  |
| Package 2 Width              | 18.500 cm |
| Package 2 Length             | 27.500 cm |
| Package 2 Weight             | 721.000 g |
| Unit Type Of Package 3       | S04       |
| Number Of Units In Package 3 | 120       |
| Package 3 Height             | 30.000 cm |
| Package 3 Width              | 40.000 cm |
| Package 3 Length             | 60.000 cm |
| Package 3 Weight             | 9.316 kg  |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Product

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |