



Product data sheet

Specifications



Sedna - single socket outlet, side earth - 16A shutters, lid, wo frame white

SDN3100121

 **Discontinued on:** Dec 30, 2023

 **Discontinued**

Main

Range Name	Sedna
Function	Socket-outlet
Delivery Form	Without frame
Outlet Poles Configuration	2P + E with shutters
Outlet Standard Description	Side earth
Rated Current	16 A at 250 V AC
Colour Code	RAL 9003
Market Segment	Small commercial Residential
Socket Additional Information	Lid

Complementary

Wire Stripping Length	13 mm
Width	71 mm
Depth	47.3 mm
Net Weight	0.073818 kg
Depth Of Visual Part	16 mm
Fixing Mode	Screws52...69 mm By screws and claws, span of claws working range:
Height	71 mm
Surface Finish	Glossy
Material Of Visible Parts	ASA + PC
Wire Structure	Flexible Rigid
Terminal Capacity	2 cable(s) 2.5 mm²
Kind Of Terminals	Screw terminals
Power Range	3680 W

Environment

Ip Degree Of Protection	IP20
Product Certifications	GOST-R
Standards	IEC 60884-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	7.000 cm
Package 1 Length	7.000 cm
Package 1 Weight	76.500 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.500 cm
Package 2 Width	18.500 cm
Package 2 Length	27.500 cm
Package 2 Weight	848.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	10.820 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations