

Product data sheet

Specifications



Sedna - double socket-outlet with side earth - 16A shutters, white

SDN3000421

 **Discontinued on:** Dec 30, 2023

 **Discontinued**

Main

Range Name	Sedna
Function	Socket-outlet
Delivery Form	Complete product
Outlet Poles Configuration	2P + E with shutters
Outlet Standard Description	Side earth
Rated Current	16 A at 250 V AC
Market Segment	Small commercial Residential

Complementary

Wire Stripping Length	13 mm
Width	84 mm
Depth	48 mm
Net Weight	0.1031 kg
Depth Of Visual Part	23.3 mm
Fixing Mode	Claws, span of claws working range: 52...69 mm Screws
Height	120 mm
Surface Finish	Glossy
Material Of Visible Parts	ASA + PC
Wire Structure	Flexible Rigid Solid stranded
Terminal Capacity	2 cable(s) 2.5 mm ²
Kind Of Terminals	Lift terminals
Power Range	3680 W

Environment

Ip Degree Of Protection	IP20
Standards	IEC 60884-1

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	8.500 cm
Package 1 Length	12.000 cm
Package 1 Weight	102.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	10.000 cm
Package 2 Width	20.500 cm
Package 2 Length	31.500 cm
Package 2 Weight	1.126 kg
Unit Type Of Package 3	S04
Number Of Units In Package 3	50
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	5.974 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations