

# Product data sheet

Specifications



## Sedna - single socket outlet, side earth - 16A shutters, lid, cream

SDN3100223

 **Discontinued on:** Dec 30, 2023

 **Discontinued**

### Main

Range	Sedna
Product Or Component Type	Socket-outlet
Outlet Standard Description	Side earth
Delivery Form	Complete product
Additional Features	Lid and shuttered
Rated Current	16 A at 250 V AC
Cover Plate Color	Cream
Kind Of Terminals	Lift terminals

### Complementary

Installation	Flush
Power Range	3680 W
Terminal Capacity	2 cable(s) 2.5 mm <sup>2</sup>
Wire Structure	Rigid Flexible
Wire Stripping Length	13 mm
Material Of Visible Parts	ASA + PC
Surface Finish	Glossy
Fixing Mode	Screws or claws 52...69 mm
Height	80 mm
Width	85 mm
Depth	47.3 mm
Depth Of Visual Part	16 mm
Net Weight	0.074818 kg

### Environment

Ip Degree Of Protection	IP20
-------------------------	------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	5.000 cm
Package 1 Width	11.000 cm
Package 1 Length	15.000 cm
Package 1 Weight	104.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	10.000 cm
Package 2 Width	20.500 cm
Package 2 Length	31.000 cm
Package 2 Weight	731.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	30
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	4.019 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations