

# Product data sheet

Specifications



## Sedna - TV-SAT ending outlet - 1dB without frame titanium

SDN3401668

 **Discontinued on:** Dec 30, 2023

 **Discontinued**

### Main

Range Name	Sedna
Range	Sedna
Function	TV/SAT socket
Delivery Form	Without frame
Tv Socket Type	End-of-line (terminal socket)
Cover Plate Color	Titanium

### Complementary

Tv Connector Type	1 male IEC 9.52 mm
Sat Connector Type	1 F type
Number Of Outputs	2
Through Loss	1 dB
Attenuation	1 dB for TV signal for 5...862 MHz frequency 1 dB for SAT signal for 950...2400 MHz frequency
Connections - Terminals	Screw terminals
Material Of Visible Parts	Thermoplastic ABS-UV stabilised
Kind Of Terminals	Glossy
Installation	Flush
Fixing Mode	Claws, span of claws working range: 55...70 mm Screws
Height	70 mm
Width	64 mm
Depth	40.5 mm
Depth Of Visual Part	17.4 mm
Net Weight	0.10226 kg

### Environment

Conformity Mark	CE
Ip Degree Of Protection	IP20

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	6.500 cm
Package 1 Length	7.000 cm
Package 1 Weight	79.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.500 cm
Package 2 Width	18.500 cm
Package 2 Length	27.500 cm
Package 2 Weight	860.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	10.908 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations