

# Product data sheet

Specifications



## Sedna - horizontal 2-gang frame - graphite

SDN5800370

⚠ Discontinued on: Dec 30, 2023

⚠ Discontinued

### Main

Range Name	Sedna
Range	Sedna
Device Application	Mounting
Function	Cover frame
Number Of Gangs	2 gangs
Installation Direction	Horizontal
Range Compatibility	Sedna socket-outlet
Cover Frame Color	Graphite

### Complementary

Material Of Visible Parts	Thermoplastic ABS-UV stabilised
Surface Finish	Glossy
Height	80 mm
Width	156 mm
Depth	7 mm
Depth Of Visual Part	7 mm
Net Weight	0.0275 kg

### Environment

Ip Degree Of Protection	IP20
-------------------------	------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	8.000 cm
Package 1 Length	15.500 cm
Package 1 Weight	22.500 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	25
Package 2 Height	10.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	20.500 cm
Package 2 Length	32.500 cm
Package 2 Weight	691.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	125
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	4.119 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations