


Product data sheet

Specifications



Sedna - tel+data outlet - RJ11 + RJ45 cat.6 UTP without frame titanium

SDN5200168

⚠ Discontinued on: Dec 30, 2023

⚠ Discontinued

Main

Range Name	Sedna
Range	Sedna
Device Application	Communication
Function	Telephone + data outlet
Delivery Form	Without frame
Cover Plate Color	Titanium
Market Segment	Small commercial Residential

Complementary

Socket Number	2
Wire Structure	Rigid
Kind Of Terminals	Screw terminals: RJ11 Screw terminals: RJ45
Material Of Visible Parts	Thermoplastic ABS-UV stabilised
Surface Finish	Glossy
Installation Direction	Straight
Installation	Flush
Fixing Mode	Claws, span of claws working range: 48...81 mm Screws
Height	71 mm
Width	71 mm
Depth	36 mm
Depth Of Visual Part	14.5 mm
Net Weight	0.05886 kg

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	4.000 cm
Package 1 Width	7.500 cm
Package 1 Length	7.500 cm
Package 1 Weight	60.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.500 cm
Package 2 Width	18.500 cm
Package 2 Length	27.500 cm
Package 2 Weight	683.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	8.723 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations