

Product data sheet

Specifications



Sedna - cable outlet - without frame beige

SDN5500147

⚠ Discontinued on: Dec 30, 2023

⚠ Discontinued

Main

Range Name	Sedna
Range	Sedna
Function	Cable outlet
Device Mounting	Flush
Delivery Form	Mechanism with fixing frame
Rated Current	25 A at 250 V AC

Complementary

Colour	Beige
Fixing Of Mechanism	Screws and claws
Material Of Visible Parts	ABS (acrylonitrile butadiene-styrene)
Surface Finish	Satin
Connections - Terminals	Screwless terminals
Fixing Mode	Screws or claws, span of claws working range: 56...74 mm
Height	58 mm
Width	73 mm
Depth	73 mm
Depth Of Visual Part	31 mm
Net Weight	0.067 kg
Targeted Channel	Professional

Environment

Conformity Mark	AENOR
Product Certifications	CE
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	7.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	7.000 cm
Package 1 Weight	61.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	10.000 cm
Package 2 Width	18.500 cm
Package 2 Length	27.500 cm
Package 2 Weight	712.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	9.087 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations