

Product data sheet

Specifications



Serial line cartridge, Modicon M221, conveying 1 I/O extension

TMC2CONV01

Main

Range Of Product	Modicon M221
Product Or Component Type	Serial line cartridge
Product Compatibility	Modicon M221C
Product Specific Application	Conveying applications

Complementary

Integrated Connection Type	Non isolated serial link - screw terminal block for RS232 Non isolated serial link - screw terminal block for RS485
Transmission Rate	1.2...115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2...115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232
Communication Port Protocol	Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network
Insulation	Non-insulated between lines and internal logic
Height	41 mm
Depth	15 mm
Width	35 mm
Net Weight	0.015 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	4.6 cm
Package 1 Length	7.0 cm
Package 1 Weight	20.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	75
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.68 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	2400

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Height	75 cm
Package 3 Width	40 cm
Package 3 Length	80 cm
Package 3 Weight	57 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov