

Product data sheet

Specifications



Voltage Presence Indicating Systems, PowerLogic VPIS, IEC 62271-206, V3, 15.5µA

VPI62605

Main

| | |
|---|------------------------------------|
| Master Range | PowerLogic |
| Range Of Product | PowerLogic VPIS |
| Product Or Component Type | Voltage presence indicating system |
| Device Short Name | VPIS V3 |
| Network Type | AC |
| Type Of Installation | Indoor |
| Standards | IEC 62271-206:2011 |
| Rated Frequency (Fr) | 50/60 Hz |
| Current Threshold | 15.5 µA |
| Voltage Output Option | Without |
| Degrees Of Protection Provided By Enclosures (Ip Code) | IP3X |
| Degree Of Protection Of Enclosure Against External Mechanical Impacts (Ik Code) | IK05 |

Complementary

| | |
|--------|-------|
| Mass | 85 g |
| Height | 35 mm |
| Width | 70 mm |
| Depth | 40 mm |

Environment

| | |
|---------------------------------------|--|
| Electromagnetic Compatibility | Electrostatic discharge immunity test conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 Damped oscillatory wave immunity test conforming to IEC 61000-4-18 |
| Ambient Air Temperature For Operation | -25...85 °C |
| Ambient Air Temperature For Storage | -40...85 °C |
| Humidity Conditions | Average relative humidity over 24 h <= 95 % |
| Operating Altitude | < 1000 m |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|----------|
| Package 1 Height | 4.2 cm |
| Package 1 Width | 10 cm |
| Package 1 Length | 15 cm |
| Package 1 Weight | 36 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 14 |
| Package 2 Height | 9 cm |
| Package 2 Width | 9.2 cm |
| Package 2 Length | 26.7 cm |
| Package 2 Weight | 1.13 kg |
| Unit Type Of Package 3 | S03 |
| Number Of Units In Package 3 | 168 |
| Package 3 Height | 30 cm |
| Package 3 Width | 30 cm |
| Package 3 Length | 40 cm |
| Package 3 Weight | 6.448 kg |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |