

Product data sheet

Specifications



Roda - assembled 2 USB charger 2.1A 127/220V - white

WDA65921

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range Of Product	Roda
Product Or Component Type	USB charger
Fixing Mode	Fixed
Integrated Connection Type	2 USB port 5 V DC, maximum load current: 2.1 A

Complementary

Device Mounting	Flush
Device Presentation	Assembly
Range Compatibility	Roda
Colour Tint	White
Surface Finish	Matt
Surface Treatment	Untreated
Number Of Modules	1 x 2 modules
Type Of Packing	Bag
Quantity Per Set	Set of 10
Sale Per Indivisible Quantity	1
Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-5...50 °C
Relative Humidity	15...95 %
Connector Type	USB 2.0
[Ue] Rated Operational Voltage	100/240 V AC at 50/60 Hz
Power Consumption In W	0.1 W
Input Power	10 W
Maximum Load Current With 2 Outputs Used Simultaneously	1 A
Material	Thermoplastic ABS-UV stabilised: centre plate PC (polycarbonate) GF10 FR: casing PC (polycarbonate): centre plate
Protection Type	Short time short-circuit protection
Number Of Terminals	2 screw terminals
Screwdriver Shape	Phillips combined

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Clamping Connection Capacity	1.5...2.5 mm² for flexible cable(s)
	1.5...2.5 mm² for rigid cable(s)
Wire Stripping Length	7 mm
Product Compatibility	Emblaze mobile Qualcomm Sony Ericsson Apple Research in Motion TCT mobile (ALCATEL) Huawei Technologies Samsung Nokia Texas Instruments Atmel Motorola Mobility LGE
Height	124 mm
Width	85 mm
Depth	48 mm

Environment

Standards	ETSI EN 300 489-34 EN 60950-1 EN 62684 NEMA 5-15R
Directives	2006/95/EC - low voltage directive 2004/108/EC - electromagnetic compatibility 2009/125/EC - ecodesign
Electrical Insulation Class	Class II
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20
Environmental Characteristic	Petrol Window-cleaning fluid Hydrogen peroxide (H2O2) Alcohol Oil Acetone Bleach UV resistant Liquid soap

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	13 cm
Package 1 Length	19 cm
Package 1 Weight	100 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	18 cm
Package 2 Width	14 cm
Package 2 Length	25 cm
Package 2 Weight	1005 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Under investigation
-------------------	---------------------
