

# Product data sheet

Specifications



## Exxact indication sign "UPPTAGET" 24V red lense white

WDE002358

### Main

Range	Exxact
Product Or Component Type	Light signal
Quantity Per Set	Set of 1

### Complementary

Device Mounting	Flush
Rated Voltage	24 V
Colour	White (RAL 9003)
Local Signalling	Red LED E10
Cap/Operator Or Lens Colour	Red
Connections - Terminals	Screwless terminals
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm² for solid cable(s) 1 x 1.5...2 x 2.5 mm² for solid stranded cable(s)
Material	ABS + PC
Fixing Mode	By screws
Embedding Depth	23 mm
Height	71 mm
Width	71 mm
Projecting Depth	24 mm

### Environment

Standards	EN 62094-1
Product Certifications	NEMKO CE FIMKO SEMKO
Ip Degree Of Protection	IP20

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.900 cm
Package 1 Width	8.100 cm
Package 1 Length	7.900 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	76.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	29.400 cm
Package 2 Width	28.800 cm
Package 2 Length	39.200 cm
Package 2 Weight	2.270 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	1080
Package 3 Height	80.000 cm
Package 3 Width	115.500 cm
Package 3 Length	120.000 cm
Package 3 Weight	121502.000 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations