

Product data sheet

Specifications



Socket-outlet, Exxact, mechanism with fixing frame, 2P + E, 16A, Schuko, with shutter, screwless terminals anthracite

WDE003577

Main

Range	Exxact
Product Or Component Type	Socket-outlet
Device Application	Power supply
Device Presentation	Mechanism with fixing frame
Socket Number	1
Outlet Standard	CEE 7/3
Outlet Standard Deviation	Schuko
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Colour Tint	Anthracite (RAL 7021)
Quantity Per Set	Set of 10

Complementary

Device Mounting	Flush
Outlet Poles Configuration	2P + E
Rated Current	16 A
Cover Type	With shutter
Fixing Mode	By screws
Connections - Terminals	Screwless terminals
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm ² for solid cable(s) 1 x 1.5...2 x 2.5 mm ² for solid stranded cable(s)
Material	ASA + PC
Depth	47.0 mm
Embedding Depth	28 mm
Height	71 mm
Width	71 mm
Projecting Depth	19 mm

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	SS 4280834
	IEC 60884-1
	SFS 5610:2004
	DIN VDE 0620-1
Product Certifications	SEMKO
	NEMKO
	FIMKO

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.200 cm
Package 1 Width	7.200 cm
Package 1 Length	7.600 cm
Package 1 Weight	80.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.400 cm
Package 2 Width	27.600 cm
Package 2 Length	18.200 cm
Package 2 Weight	900.000 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

✓ Sustainable Packaging

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations