

Product data sheet

Specifications



2 Socket-outlet, Exxact, mechanism with fixing frame, 2P + E, 16A, Schuko, with shutter, screwless terminals anthracite

WDE003585

Main

Range	Exxact
Product Or Component Type	Socket-outlet
Device Application	Power supply
Device Presentation	Mechanism with fixing frame
Socket Number	2
Outlet Standard	CEE 7/3
Outlet Standard	Schuko
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Colour Tint	Anthracite (RAL 7021)
Quantity Per Set	Set of 5

Complementary

Device Mounting	Flush
Outlet Poles Configuration	2P + E
Rated Current	16 A
Cover Type	With shutter
Fixing Mode	By claw kit
Connections - Terminals	Screwless terminals
Number Of Loop Terminals	2
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm² for solid cable(s) 1 x 1.5...2 x 2.5 mm² for solid stranded cable(s)
Material	ASA + PC
Depth	44.2 mm
Embedding Depth	22.4 mm
Height	88.1 mm
Width	71 mm
Projecting Depth	21.8 mm

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	SS 4280834 DIN VDE 0620-1 SFS 5610:2004 IEC 60884-1
Product Certifications	SEMKO NEMKO FIMKO

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.600 cm
Package 1 Width	8.800 cm
Package 1 Length	10.700 cm
Package 1 Weight	92.000 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

✔ Sustainable Packaging

Well-being performance

✔ Reach Free Of Svhc

✔ Toxic Heavy Metal Free

✔ Mercury Free

✔ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations