

# Product data sheet

Specifications



## SELV push-button, Exxact, 2-pole, anthracite

WDE003392

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

|                           |                       |
|---------------------------|-----------------------|
| Range Of Product          | Exxact                |
| Range                     | Exxact                |
| Product Or Component Type | SELV push-button      |
| Colour Tint               | Anthracite (RAL 7021) |
| Quantity Per Set          | Set of 1              |

### Complementary

|                              |   |
|------------------------------|---|
| Device Presentation          | Mechanism with fixing frame   |
| Device Mounting              | Flush   |
| Switch Function              | 1-pole 1-way  |
| Number Of Rocker             | 2   |
| Local Signalling             | Red LED light when activated  |
| Connections - Terminals      | Screw terminals   |
| Clamping Connection Capacity | <= 1.5 mm² for solid cable(s)<br><= 1.5 mm² for solid stranded cable(s) |
| Material                     | ABS (acrylonitrile butadiene-styrene)                                   |
| Embedding Depth              | 24 mm   |
| Height                       | 71 mm   |
| Width                        | 71 mm   |
| Projecting Depth             | 13 mm   |

### Environment

|                         |      |
|-------------------------|------|
| Ip Degree Of Protection | IP20 |
|-------------------------|------|

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 3.8 cm |
| Package 1 Width              | 7.1 cm |
| Package 1 Length             | 7.1 cm |
| Package 1 Weight             | 1 kg   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

|  |   |
|--|---|
|  Mercury Free               |   |
|  Rohs Exemption Information | <a href="#">Yes</a>   |
| Reach Regulation   | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive  | Compliant with Exemptions   |
| China Rohs Regulation  | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information       |
| Weee   | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |