

Product data sheet

Specifications



Socket-outlet with timer, Exxact, mechanism with fixing frame, 2P + E, 8A, Schuko anthracite

WDE003469

⚠ Discontinued on: May 9, 2023

⚠ Discontinued

Main

Range	Exxact
Product Or Component Type	Socket-outlet with timer
Quantity Per Set	1 piece

Complementary

Device Presentation	Mechanism with fixing frame
Device Mounting	Flush
Technology Type	Electronic
Switch Function	2-pole
Rated Current	8 A
Outlet Poles Configuration	2P + E
Outlet Standard	Schuko
Rated Voltage	230 V AC
Power Range	Motor: 1000 W Incandescent lamp: 1840 W 230 V AC halogen lamp: 1500 W
Colour Tint	Anthracite
Local Signalling	Green LED indication in active position
Time Delay Range	15 min...8 h
Connections - Terminals	Screw terminals
Shape Of Screw Head	Pozidriv No 1 and combi
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm ² for solid cable(s) 1 x 1.5...2 x 2.5 mm ² for solid stranded cable(s)
Material	PC
Protection Type	Electronic overload and temperature protection
Embedding Depth	30 mm
Height	71 mm
Width	71 mm
Projecting Depth	32 mm

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60669-1 IEC 60884-1 EN 60669-2-1 EN 60669-2-3
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.8 cm
Package 1 Width	7.2 cm
Package 1 Length	9.6 cm
Package 1 Weight	170 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	16.4 cm
Package 2 Width	16.8 cm
Package 2 Length	27.2 cm
Package 2 Weight	1.858 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	20
Package 3 Height	19.2 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.078 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations