

# Product data sheet

Specifications



## 2 Socket-outlet, Exxact, mechanism with fixing frame, 2P + E, 16A, Schuko, with shutter,metallic

WDE004287

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

|                                |                             |
|--------------------------------|-----------------------------|
| Range                          | Exxact                      |
| Product Or Component Type      | Socket-outlet               |
| Device Application             | Power supply                |
| Device Presentation            | Mechanism with fixing frame |
| Socket Number                  | 2                           |
| Outlet Standard                | CEE 7/3                     |
| Outlet Standard                | Schuko                      |
| [Ue] Rated Operational Voltage | 250 V                       |
| Network Type                   | AC                          |
| Colour Tint                    | Metallic                    |
| Quantity Per Set               | Set of 5                    |

### Complementary

|                              |   |
|------------------------------|---|
| Device Mounting              | Flush   |
| Outlet Poles Configuration   | 2P + E  |
| Rated Current                | 16 A  |
| Cover Type                   | With shutter  |
| Fixing Mode                  | By claw kit   |
| Connections - Terminals      | Screw terminals   |
| Number Of Loop Terminals     | 2   |
| Shape Of Screw Head          | Pozidriv No 1 and combi   |
| Clamping Connection Capacity | 1 x 1.5...2 x 2.5 mm <sup>2</sup> for solid cable(s)<br>1 x 1.5...2 x 2.5 mm <sup>2</sup> for solid stranded cable(s) |
| Material                     | ASA + PC  |
| Depth                        | 44.2 mm   |
| Embedding Depth              | 32.4 mm   |
| Height                       | 88.1 mm   |
| Width                        | 71 mm   |
| Projecting Depth             | 11.8 mm   |

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                         |  |
|-------------------------|--|
| Ip Degree Of Protection | IP20   |
| Standards               | VDE 0620-1<br>SFS 5610:2004<br>SS 4280834<br>IEC 60884-1<br>NEK 502:2006 |
| Product Certifications  | NEMKO<br>FIMKO<br>SEMKO  |

## Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type Of Package 1       | PCE        |
| Number Of Units In Package 1 | 1          |
| Package 1 Height             | 8.8 cm     |
| Package 1 Width              | 5.7 cm     |
| Package 1 Length             | 1.2 cm     |
| Package 1 Weight             | 100 g      |
| Unit Type Of Package 2       | CAR        |
| Number Of Units In Package 2 | 5          |
| Package 2 Height             | 9.3 cm     |
| Package 2 Width              | 10.1 cm    |
| Package 2 Length             | 26 cm      |
| Package 2 Weight             | 618 g      |
| Unit Type Of Package 3       | P12        |
| Number Of Units In Package 3 | 1440       |
| Package 3 Height             | 80 cm      |
| Package 3 Width              | 114.9 cm   |
| Package 3 Length             | 120 cm     |
| Package 3 Weight             | 206.872 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging   Transparency   RoHS/REACH

## Resource performance

✓ Sustainable Packaging

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |