

Product data sheet

Specifications



Cover frame, Exxact Design, 2 gangs, white

WDE004342

Main

Range	Exxact
Aesthetic Name	Design
Product Or Component Type	Cover frame
Number Of Gangs	2 gangs
Colour Tint	White
Quantity Per Set	Set of 5

Complementary

Device Mounting	Flush Surface
Material	ABS + glass
Standards	EN 60669-1 IEC 60884-1
Product Certifications	SEMKO CE FIMKO NEMKO
Ip Degree Of Protection	IP44 with additional sealing kit IP20
Height	158 mm
Width	87 mm
Depth	11.6 mm
Function Available	Possibility to put wallpaper, pictures etc instead of the inlays

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	10.400 cm
Package 1 Length	16.000 cm
Package 1 Weight	52.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	8.800 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	16.300 cm
Package 2 Length	10.500 cm
Package 2 Weight	274.000 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	30
Package 3 Height	12.400 cm
Package 3 Width	29.800 cm
Package 3 Length	39.000 cm
Package 3 Weight	2.006 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations