

Product data sheet

Specifications



Double socket-outlet, Exxact, complete product, 2P + E, 16A, Schuko, 45° ground lug, with shutter, white

WDE008286

Main

Range	Exxact
Product Or Component Type	Socket-outlet
Device Application	Power supply
Device Presentation	Complete product
Socket Number	2
Outlet Standard	CEE 7/3
Outlet Standard	Schuko
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Colour Tint	White (RAL 9003)

Complementary

Device Mounting	Flush
Outlet Poles Configuration	2P + E
Ground Lug Position	45° ground lug
Rated Current	16 A
Cover Type	With shutter
Fixing Mode	By claw kit
Connections - Terminals	Screw terminals
Number Of Loop Terminals	1
Shape Of Screw Head	Pozidriv No 1 and combi
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm² for solid cable(s) 1 x 1.5...2 x 2.5 mm² for solid stranded cable(s)
Material	ASA + PC
Depth	44.3 mm
Embedding Depth	22.3 mm
Height	87 mm
Width	87 mm
Projecting Depth	22 mm

Environment

Ip Degree Of Protection	IP21
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	NEK 502:2006
	IEC 60884-1
	DIN VDE 0620-1
	SS 4280834
	SFS 5610:2004
Product Certifications	FIMKO

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	8.7 cm
Package 1 Length	3.7 cm
Package 1 Weight	96.4 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations