

Product data sheet

Specifications



Data socket, Exxact, complete product, Cat6, UTP, straight, metallic

WDE008761

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

| | |
|---------------------------|------------------|
| Range | Exxact |
| Product Or Component Type | Data socket |
| Device Presentation | Complete product |

Complementary

| | |
|------------------------|---------------------------------------|
| Device Mounting | Flush |
| Socket Number | 2 |
| Cable Shielding Type | UTP |
| Installation Direction | Straight |
| Cover Type | Label holder |
| Data Socket Type | RJ45 Cat.6 |
| Colour Tint | Metallic |
| Range Compatibility | LexCom |
| Number Of Modules | 2 modules |
| Material | ABS (acrylonitrile butadiene-styrene) |
| Width | 87 mm |
| Height | 87 mm |
| Depth | 35 mm |
| Embedding Depth | 20 mm |

Environment

| | |
|-------------------------|-----------------------------|
| Ip Degree Of Protection | IP20 |
| Standards | EN 50173-1 IEC 60603-7-4 |

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.7 cm |
| Package 1 Width | 8.7 cm |
| Package 1 Length | 3.6 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|--------|
| Package 1 Weight | 89.0 g |
|------------------|--------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | | |
|-----------------------|---|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |
| | | |
| Reach Regulation | REACH Declaration | |
| Eu Rohs Directive | Compliant EU RoHS Declaration | |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) | |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins | |
| Circularity Profile | No need of specific recycling operations | |