

Product data sheet

Specifications



Switch, Exxact Surface, complete product, 3-pole 1-way, 10A, screwless terminals, white

WDE015511

Main

Range	Exxact
Product Or Component Type	Switch
Device Application	Control
Technology Type	Electromechanical
Quantity Per Set	Set of 5

Complementary

Device Presentation	Complete product
Device Mounting	Surface
Number Of Rocker	1
Switch Function	3-pole 1-way
Switch Pattern	[3]
Rated Current	10 A
[Ue] Rated Operational Voltage	400 V
Network Type	AC
Colour	White (RAL 9003)
Connections - Terminals	Screwless terminals
Loop Terminals	0.0
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm² for solid cable(s) 1 x 1.5...2 x 2.5 mm² for solid stranded cable(s)
Material	PC 10 % GF: bottom-plate PC (polycarbonate): cover frame PC/ABS: rocker
Optional Fixing Mode	By screw: insert By click-in: cover By click-in: rocker
Height	75.0 mm
Width	65.0 mm
Projecting Depth	27.0 mm
Marking	0 - 1

Environment

Standards	EN 60669-1
-----------	------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	CE
	FIMKO
	NEMKO
	SEMKO
Ip Degree Of Protection	IP20
	IP21 when cable is coming from below

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	72.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations