

Product data sheet

Specifications



Renova Surface Single Socket-Outlet Schuko with screw terminals white

WDE015877

Main

Range	Renova
Product Or Component Type	Socket-outlet
Device Presentation	Complete product
Quantity Per Set	Set of 10

Complementary

Socket Number	1
Device Mounting	Surface
Outlet Poles Configuration	2P + E
Outlet Standard	Schuko
Outlet Standard	CEE 7/3
Rated Current	16 A
[Ue] Rated Operational Voltage	250 V AC
Colour Tint	White (RAL 9010)
Connections - Terminals	Screw terminals
Shape Of Screw Head	Pozidriv No 1 and combi
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm² for solid cable(s) 1 x 1.5...2 x 2.5 mm² for solid stranded cable(s)
Material	PC (polycarbonate): cover frame PC 10 % GF: bottom-plate
Fixing Mode	By screws: insert By screw: cover frame
Diameter	70.0 mm
Embedding Depth	0.0 mm
Projecting Depth	43.0 mm

Environment

Standards	DIN VDE 0620-1 IEC 60884-1 NEK 502 SFS 5610 SS 4280834
Product Certifications	FIMKO NEMKO SEMKO CE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.3 cm
Package 1 Width	6.9 cm
Package 1 Length	6.9 cm
Package 1 Weight	64.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.4 cm
Package 2 Width	17.6 cm
Package 2 Length	26.0 cm
Package 2 Weight	764.0 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	120
Package 3 Height	30.0 cm
Package 3 Width	40.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	9.96 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations