

# Product data sheet

Specifications



## Uni-Telway/Modbus serial link - L = 20 m - 1 male mini DIN + 1 male SUB-D 25

XBTZ9687

⚠ Discontinued on: Dec 23, 2022

⚠ Discontinued

### Main

|                                       |                               |
|---------------------------------------|-------------------------------|
| Range Of Product                      | Magelis XBT                   |
| Accessory / Separate Part Category    | Connection accessories        |
| Accessory / Separate Part Type        | Connecting cable              |
| Accessory / Separate Part Designation | Uni-Telway/Modbus serial link |
| Accessory / Separate Part Destination | XBT terminal                  |
| Cable Length                          | 20 m                          |

### Complementary

|                             |  |
|-----------------------------|--|
| Product Compatibility       | All Magelis XBTN/R except XBT N200/N400 and XBT R400           |
| Range Compatibility         | Twido<br>Modicon Premium automation platform                   |
| Electrical Connection       | 1 male connector mini DIN, 8 pins<br>1 male connector SUB-D 25 |
| Communication Port Protocol | Uni-Telway<br>Modbus   |
| Physical Interface          | RS485  |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 3.0 cm   |
| Package 1 Width              | 30.0 cm  |
| Package 1 Length             | 36.0 cm  |
| Package 1 Weight             | 1.09 kg  |
| Unit Type Of Package 2       | S02      |
| Number Of Units In Package 2 | 5        |
| Package 2 Height             | 15.0 cm  |
| Package 2 Width              | 30.0 cm  |
| Package 2 Length             | 40.0 cm  |
| Package 2 Weight             | 5.905 kg |

### Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

## Sustainability



**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

|  |   |
|--|---|
|  Mercury Free               |   |
|  Rohs Exemption Information | <a href="#">Yes</a>   |
| Reach Regulation   | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive  | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation  | <a href="#">China RoHS declaration</a>  |
| Weee   | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins   |
| California Proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |