

# Product data sheet

Specifications



Fixing base, Harmony XVB, for modular tower lights, plastic, 70mm, 80mm black aluminium support tube + black fixing plate

XVBZ02

## Main

Range Of Product	Harmony XVB
Accessory / Separate Part Designation	Fixing base
Product Or Component Type	Fixing base
Accessory / Separate Part Category	Mounting and fixing accessories
Accessory / Separate Part Destination	Beacons and indicator banks Ø 70 mm

## Complementary

Accessory / Separate Part Type	Fixing base
Product Compatibility	XVBL. XVBC.
Kit Composition	Black plastic fixing plate Ø 25 mm aluminium support tube
Height Under Base Unit	80 mm
Colour	Black aluminium
Net Weight	0.11 kg

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.970 cm
Package 1 Width	6.993 cm
Package 1 Length	11.973 cm
Package 1 Weight	87.000 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	100
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	9.260 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	400
Package 3 Height	77.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	45.540 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free


✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

Dimensions Drawings

Dimensions and Mounting



Height under base unit	
b in mm	b in in.
80	3.15

Mounting and Clearance

Panel Cut-Out

---

