

INTERNAL ONLY

Issue: How to setup an EcoAisle Cold Containment with different size units.

Product line: EcoAisle

Environment: All

Cause: Install

Resolution:

Cold aisle containment dimensions

1200	1200	1070	1200	1070	900
COLD AISLE					
1200	1070	1070	900	900	900

		Nominal Aisle Width					
Cold Aisle - Middle of Aisle, Frame to Frame, With Depth Extenders	914 (36)	991 (39)	1121 (44.13)	1251 (49.25)	--	1121 (44.13)	--
		--	991 (39.00)	1121 (44.13)	--	1121 (44.13)	--
		--	--	991 (39.00)	--	--	--
		--	--	--	--	--	--
		--	--	--	--	--	--
		--	--	--	--	--	--
	1219 (48)	1296 (51.02)	1426 (56.14)	1556 (61.26)	1296 (51.02)	1426 (56.14)	1296 (51.02)
		--	1296 (51.02)	1426 (56.14)	1296 (51.02)	1426 (56.14)	1296 (51.02)
		--	--	1296 (51.02)	1166 (45.91)	1296 (51.02)	1296 (51.02)
		--	--	--	1296 (51.02)	1426 (56.14)	1296 (51.02)
		--	--	--	--	1296 (51.02)	1296 (51.02)
		--	--	--	--	--	1296 (51.02)
	1524 (60)	1600 (63.00)	1730 (68.11)	1860 (73.23)	1600 (63.00)	1730 (68.11)	1600 (63.00)
		--	1600 (63.00)	1730 (68.11)	1600 (63.00)	1730 (68.11)	1600 (63.00)
		--	--	1600 (63.00)	1470 (57.88)	1600 (63.00)	1600 (63.00)
		--	--	--	1600 (63.00)	1730 (68.11)	1600 (63.00)
		--	--	--	--	1600 (63.00)	1600 (63.00)
		--	--	--	--	--	1600 (63.00)
	1829 (72)	1905 (75.00)	2035 (80.12)	2165 (85.24)	1905 (75.00)	--	1905 (75.00)
		--	1905 (75.00)	2035 (80.18)	1905 (75.00)	--	1905 (75.00)
		--	--	1905 (75.00)	1775 (69.88)	1905 (75.00)	1905 (75.00)
		--	--	--	1905 (75.00)	--	1905 (75.00)
		--	--	--	--	1905 (75.00)	1905 (75.00)
		--	--	--	--	--	1905 (75.00)

Cold Aisle - End of Aisle, Frame to Frame, No Depth Extenders	914 (36.00)	991 (39.00)	991 (39.00)	991 (39.00)	--	--	--
	1219 (48.00)	1296 (51.02)	1296 (51.02)	1296 (51.02)	1296 (51.02)	1296 (51.02)	1296 (51.02)
	1524 (60.00)	1600 (63.00)	1600 (63.00)	1600 (63.00)	1600 (63.00)	1600 (63.00)	1600 (63.00)
	1829 (72.00)	1905 (75.00)	1905 (75.00)	1905 (75.00)	1905 (75.00)	1905 (75.00)	1905 (75.00)

* All dimensions shown in millimeters (inches).

