

Product data sheet

Specifications

MODULAR DEVICE RAIL

01260



⚠ Discontinued on: Nov 29, 2021

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Rail
Accessory / Separate Part Category	Installation accessory
Type Of Rail	Modular
Installed Device	Acti 9: fixed C120 without earth leakage protection - control: toggle Vigilohm: EM9 TeSys: GV2 TeSys: fixed GV2L TeSys: fixed GV2LE TeSys: fixed GV2ME TeSys: fixed GV2P TeSys: fixed GV2RTn TeSys: fixed GV3 Acti 9: fixed iC120 without earth leakage protection - control: toggle Vigilohm: IM20 Vigilohm: IM20H Vigilohm: fixed IM9 Vigilohm: fixed IM9-OL ComPact: fixed INS100 - control: direct front rotary handle - vertical installation ComPact: fixed INS160 - control: direct front rotary handle - vertical installation ComPact: fixed INS40 - control: direct front rotary handle - vertical installation ComPact: fixed INS63 - control: direct front rotary handle - vertical installation Acti 9: fixed modular device Multi9: fixed modular device Gould fuse: modular fusegear Multi9: fixed NG125 without earth leakage protection - control: toggle Multi9: fixed NG125 NA - control: toggle relay Vigirex: RH10 Vigirex: RH21 Vigirex: RH99 Vigilohm: SM21 Vigilohm: TR5A Acti 9: fixed C120 with earth leakage protection - control: toggle Acti 9: fixed iC120 with earth leakage protection - control: toggle Multi9: fixed NG125 with earth leakage protection - control: toggle

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Poles Description	1 x 3P: fixed C120 1 x 4P: fixed C120 9 x 3P: fixed GV2L 9 x 3P: fixed GV2LE 9 x 3P: fixed GV2ME 9 x 3P: fixed GV2P 9 x 3P: fixed GV2RTn 7 x 3P: fixed GV3 1 x 3P: fixed iC120 1 x 4P: fixed iC120 1 x 3P: fixed INS100 vertical installation 1 x 4P: fixed INS100 vertical installation 1 x 3P: fixed INS160 vertical installation 1 x 4P: fixed INS160 vertical installation 1 x 3P: fixed INS40 vertical installation 1 x 4P: fixed INS40 vertical installation 1 x 3P: fixed INS63 vertical installation 1 x 4P: fixed INS63 vertical installation 1 x 3P: fixed NG125 1 x 4P: fixed NG125 1 x 3P: fixed NG125 NA 1 x 4P: fixed NG125 NA
-------------------	---

Complementary

Installation Description	Pack enclosure - width 555 mm
Number Of Vertical Modules [50 Mm]	5 module(s): C120 without earth leakage protection , direct in 555 mm WidePack enclosure 3 module(s): GV2 in 555 mm WidePack enclosure 3 module(s): GV2L, direct in 555 mm WidePack enclosure 3 module(s): GV2LE, direct in 555 mm WidePack enclosure 3 module(s): GV2ME, direct in 555 mm WidePack enclosure 3 module(s): GV2P, direct in 555 mm WidePack enclosure 3 module(s): GV2RTn, direct in 555 mm WidePack enclosure 5 module(s): GV3, direct in 555 mm WidePack enclosure 5 module(s): iC120 without earth leakage protection , direct in 555 mm WidePack enclosure 3 module(s): IM20 in 555 mm WidePack enclosure 3 module(s): IM20H in 555 mm WidePack enclosure 3 module(s): IM9 in 555 mm WidePack enclosure 3 module(s): IM9-OL in 555 mm WidePack enclosure 4 module(s): INS100, direct in 555 mm WidePack enclosure 6 module(s): INS160, direct in 555 mm WidePack enclosure 4 module(s): INS40, direct in 555 mm WidePack enclosure 4 module(s): INS63, direct in 555 mm WidePack enclosure 5 module(s): NG125 without earth leakage protection , direct in 555 mm WidePack enclosure 5 module(s): NG125 NA, direct in 555 mm WidePack enclosure 3 module(s): RH10, direct in 555 mm WidePack enclosure 3 module(s): RH21, direct in 555 mm WidePack enclosure 3 module(s): RH99, direct in 555 mm WidePack enclosure 5 module(s): C120 with earth leakage protection , direct in 555 mm WidePack enclosure 5 module(s): iC120 with earth leakage protection , direct in 555 mm WidePack enclosure 5 module(s): NG125 with earth leakage protection , direct in 555 mm WidePack enclosure
9 Mm Pitches	48
Quantity Per Set	Set of 1
Height	35 mm
Width	464 mm
Depth	52 mm
Net Weight	0.25 kg
Colour	Natural
Material	Metal
Thickness	1.5 mm

Environment

Standards	IEC 61439-2
	IEC 61439-1
Product Certifications	ASEFA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	8 cm
Package 1 Length	49.5 cm
Package 1 Weight	250 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---