


Product data sheet

Specifications



MOUNTING PLATE NSX/CVS/VIGI/INS 630 V. FIX. TOGGLE

03080

 **Discontinued on:** Apr 25, 2023

 **Discontinued**

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G duct
Installation Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Installed Device	EasyPact: fixed CVS400 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS630 without earth leakage protection - control: toggle - vertical installation ComPact: fixed INS320...400 - control: direct front rotary handle - vertical installation ComPact: fixed INS500...630 - control: direct front rotary handle - vertical installation ComPact: fixed INV320...400 - control: direct front rotary handle - vertical installation ComPact: fixed INV500...630 - control: direct front rotary handle - vertical installation ComPact: fixed NSX400 without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX630 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS400 with earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS630 with earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX400 with earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX630 with earth leakage protection - control: toggle - vertical installation
Poles Description	1 x 3P: fixed CVS400 vertical installation 1 x 4P: fixed CVS400 vertical installation 1 x 3P: fixed CVS630 vertical installation 1 x 4P: fixed CVS630 vertical installation 1 x 3P: fixed INS320...400 vertical installation 1 x 4P: fixed INS320...400 vertical installation 1 x 3P: fixed INS500...630 vertical installation 1 x 4P: fixed INS500...630 vertical installation 1 x 3P: fixed INV320...400 vertical installation 1 x 4P: fixed INV320...400 vertical installation 1 x 3P: fixed INV500...630 vertical installation 1 x 4P: fixed INV500...630 vertical installation 1 x 3P: fixed NSX400 vertical installation 1 x 4P: fixed NSX400 vertical installation 1 x 3P: fixed NSX630 vertical installation 1 x 4P: fixed NSX630 vertical installation
Condition Of Using Cable Tie	Need additional plate (1M high) when installation of device is in vertical

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Vertical Modules [50 Mm]	12 module(s): CVS400 without earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
	12 module(s): CVS400 without earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
	12 module(s): CVS630 without earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
	12 module(s): CVS630 without earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
	10 module(s): INS320...400, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
	10 module(s): INS320...400, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
	12 module(s): INS500...630, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
	12 module(s): INS500...630, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
	10 module(s): INV320...400, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
	10 module(s): INV320...400, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
	12 module(s): INV500...630, direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
	12 module(s): INV500...630, direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
	12 module(s): NSX400 without earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
	12 module(s): NSX400 without earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
	12 module(s): NSX630 without earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
	12 module(s): NSX630 without earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
	13 module(s): CVS400 with earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
	13 module(s): CVS400 with earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
	13 module(s): CVS630 with earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
	13 module(s): CVS630 with earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
	14 module(s): NSX400 with earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
	14 module(s): NSX400 with earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)
	14 module(s): NSX630 with earth leakage protection , direct with long terminal shield in 300 mm Widefloor-standing duct (cable coming from top or bottom of enclosure)
	14 module(s): NSX630 with earth leakage protection , direct with long terminal shield in 300 mm Widewall-mounted duct (cable coming from top or bottom of enclosure)

Standards	IEC 61439-2
-----------	-------------

Product Certifications	ASEFA
------------------------	-------

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
----------------------	----------------------------------------------------------------------

Surface Finish	Matt Smooth
----------------	----------------

Colour	White (RAL 9001)
--------	------------------

Width	300 mm
-------	--------

Height	350 mm
--------	--------

Net Weight	0.78 kg
------------	---------

300 mm Prisma G floor-standing duct ComPact NSX400 with fixed toggle vertical 3P
1 direct with long terminal shield 14 266 mm

300 mm Prisma G wall-mounted duct ComPact NSX400 with fixed toggle vertical 3P
1 direct with long terminal shield 14 266 mm

300 mm Prisma G floor-standing duct ComPact NSX400 with fixed toggle vertical 4P
1 direct with long terminal shield 14 266 mm

300 mm Prisma G wall-mounted duct ComPact NSX400 with fixed toggle vertical 4P
1 direct with long terminal shield 14 266 mm

300 mm Prisma G floor-standing duct ComPact NSX630 with fixed toggle vertical 3P
1 direct with long terminal shield 14 266 mm

300 mm Prisma G wall-mounted duct ComPact NSX630 with fixed toggle vertical 3P
1 direct with long terminal shield 14 266 mm

300 mm Prisma G floor-standing duct ComPact NSX630 with fixed toggle vertical 4P
1 direct with long terminal shield 14 266 mm

300 mm Prisma G wall-mounted duct ComPact NSX630 with fixed toggle vertical 4P
1 direct with long terminal shield 14 266 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	22.0 cm
Package 1 Length	23.0 cm
Package 1 Weight	780.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	25
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	20.353 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---------------------------------------------------------------------------------------------------

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	-------------------------------------------------------------------------------------------------------------

Environmental Disclosure	Product Environmental Profile
--------------------------	-----------------------------------------------