



### Main

Range	Prisma
Range compatibility	Prisma P Prisma G Pack 160 Prisma Pack 250
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out Modular
Installed device	Multi 9 : fixed modular device Acti 9 : fixed modular device Vigilohm : IM20 Vigilohm : IM20H Vigilohm : IM10 Vigilohm : IM10H Compact : fixed INS40 - control: direct front rotary handle - vertical installation Compact : fixed INS63 - control: direct front rotary handle - vertical installation Compact : fixed INS100 - control: direct front rotary handle - vertical installation Compact : fixed INS125 - control: direct front rotary handle - vertical installation Compact : fixed INS160 - control: direct front rotary handle - vertical installation
Poles description	1 x 3P : modular rail support : INS100 vertical installation 1 x 4P : modular rail support : INS100 vertical installation 1 x 3P : modular rail support : INS125 vertical installation 1 x 4P : modular rail support : INS125 vertical installation 1 x 3P : modular rail support : INS160 vertical installation 1 x 4P : modular rail support : INS160 vertical installation 1 x 3P : modular rail support : INS40 vertical installation 1 x 4P : modular rail support : INS40 vertical installation 1 x 3P : modular rail support : INS63 vertical installation 1 x 4P : modular rail support : INS63 vertical installation

### Complementary

Enclosure/Cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm, depth 400 mm Pack enclosure - width 600 mm Pack enclosure - width 555 mm
-------------------------------	--

Connection position	Direct connection
9 mm pitches	48
Number of 18 mm modules per row	24
Number of vertical modules [50 mm]	4
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA
Quantity per set	Set of 1
Height	200 mm
Width	500 mm
Product weight	0.72 kg
Material	Steel
Surface finish	Smooth Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

## Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------