


Product data sheet

Specifications



FRONT PLATE INS-INV250 HORIZONTAL W600 4M

03231

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed INS250 - control: direct front rotary handle - horizontal installation ComPact: fixed INV100 - control: direct front rotary handle - horizontal installation ComPact: fixed INV160 - control: direct front rotary handle - horizontal installation ComPact: fixed INV200 - control: direct front rotary handle - horizontal installation ComPact: fixed INV250 - control: direct front rotary handle - horizontal installation
Poles Description	1 x 3P: mounting plate support: INS250 horizontal installation 1 x 4P: mounting plate support: INS250 horizontal installation 1 x 3P: mounting plate support: INV100 horizontal installation 1 x 4P: mounting plate support: INV100 horizontal installation 1 x 3P: mounting plate support: INV250 horizontal installation 1 x 4P: mounting plate support: INV250 horizontal installation 1 x 3P: mounting plate support: INV160 horizontal installation 1 x 4P: mounting plate support: INV160 horizontal installation 1 x 3P: mounting plate support: INV200 horizontal installation 1 x 4P: mounting plate support: INV200 horizontal installation
Operating Position	Horizontal

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Connection Position	Direct connection Connection block
Number Of Vertical Modules [50 Mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	200 mm
Width	500 mm
Net Weight	0.8 kg
Quantity Per Set	Set of 1

4 Life Is On Schneider Electric Apr 20, 2024

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	21.300 cm
Package 1 Length	52.000 cm
Package 1 Weight	800.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	16.600 cm
Package 2 Width	22.200 cm
Package 2 Length	53.200 cm
Package 2 Weight	8.150 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	270
Package 3 Height	65.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	233.760 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
--------------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
------------------------------	---

Environmental Disclosure	Product Environmental Profile
---------------------------------	---